

PRODUCT-DETAILS

TY225-50X

CABLE TIE 50LB 9IN UV BLACK NYLON



General Information

Extended Product Type	TY225-50X
Product ID	7TCG054360R0236
EAN	5414363061397
Catalog Description	CABLE TIE 50LB 9IN UV BLACK NYLON
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 215mm (8.46 Inches), Width of 4.8mm (0.19 Inches), Thickness of 1.3mm (0.05 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Bulk Pack

Ordering

EAN	5414363061397
UPC	786210374390

Dimensions

Product Net Width	0.19 in 4.8 mm
Product Net Depth / Length	8.46 in 215 mm

Container Information

Package Level 1 Units	1000 piece
-----------------------	------------

Package Level 1 Width	1 in 25 mm
Package Level 1 Height	14 in 356 mm
Package Level 1 Depth / Length	18 in 457 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	15.25 in 387 mm
Package Level 2 Height	11 in 279 mm
Package Level 2 Depth / Length	23.25 in 591 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Bundle Diameter	2.25 in 57.15 mm
Color	Black
Effective Date	19970425
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	CATAMOUNT FASTENING PRODUCTS
Product Type	General Purpose
Standards	UL E49405
Tensile Strength	50 lb 222 N
Thickness	0.05 in 1.3 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY225-50X
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY225-50X

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

