



SETRON, cylindrical fuse link, 22x58 mm, 25 A, gG, Un AC: 690 V

Figure similar

Model		
product brand name		SETRON
product designation		Cylindrical fuse link
General technical data		
operating class of the fuse link		gG
type of voltage of the operating voltage		AC
supply voltage at DC		250 V
Dissipation		
power loss [W]		2.9 W
power loss [W] for rated value of the current at AC in hot operating state per pole		3 W
Main circuit		
operational current rated value		25 A
Product details		
product component striker		No
Mechanical Design		
mounting position		Any, preferably vertical
net weight		52 g
Approvals Certificates		
General Product Approval		other
		Environment




[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/lowvoltage/catalogs>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW6210-1>
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/3NW6210-1>
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6210-1
CAx-Online-Generator
<http://www.siemens.com/cax>
Tender specifications
<http://www.siemens.com/specifications>



last modified:

4/11/2025 

