

3ft USB to RS232 DB9 Serial Adapter Cable - M/M

Product ID: ICUSB232SM3



The ICUSB232SM3 3ft USB to Serial Adapter Cable lets you connect DB9 RS232 serial devices to your Mac® or PC laptop or desktop computer through an available USB port, as though the computer offered an onboard DB9M connector.

Unlike typical USB to serial converter cables where the conversion takes place at the DB9 end, the StarTech.com ICUSB232SM3 features a converter chip on the USB end. Converting at the USB source overcomes the 15ft. technical limit of USB cables, allowing for a much greater serial DB-9 extension cable (50ft.+ is possible depending on the application) if necessary.

Simple to install and use, this USB to Serial adapter is a cost-effective solution that bridges the compatibility gap between modern computers and legacy serial peripherals.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Perfect for IT Administrators looking to add legacy functionality to newer notebooks, PCs and servers that lack an integrated RS232 port
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect a satellite receiver, serial modem, or PDA with serial sync

Features

- Supports serial data transfer rates of up to 1 Mbps
- No external power needed - draws power from the USB connection
- Thin, lightweight design
- Compatible with modems, printers, bar code scanners, servers, PDUs, and nearly any serial RS232 equipment
- Easy to setup and install

Hardware	Warranty	Lifetime
	Bus Type	USB 2.0
	Chipset ID	Prolific - PL2303HXD
	Industry Standards	RS232, USB 1.1/2.0
	Interface	Serial
	Port Style	Cable Adapters
	Ports	1
Performance	FIFO	192 Bytes
	Max Baud Rate	921.6 Kbps
	Serial Protocol	RS-232
Connector(s)	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male
	Connector B	1 - DB-9 (9 pin, D-Sub) Male
Software	OS Compatibility	Windows® CE 4.2, 5.2, 98SE, ME, 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2016 Mac OS® 10.6 to 10.14 Linux 2.4.x to 4.11.x <i>LTS Versions only</i>
Environmental	Humidity	0~65% RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-20°C to 80°C (-4°F to 176°F)
Physical Characteristics	Cable Length	3 ft [0.9 m]
	Enclosure Type	Plastic
	Product Height	0.6 in [15 mm]
	Product Length	36 in [914.4 mm]
	Product Weight	2.2 oz [61 g]
	Product Width	1.4 in [35 mm]
Packaging Information	Shipping (Package) Weight	2.5 oz [70 g]
What's in the Box	Included in Package	1 - USB to Serial Converter 2 - Cable Nuts

Product appearance and specifications are subject to change without notice.