

Rittal – The System.

Faster – better – everywhere.

Ex enclosures Plastic, empty enclosure with hinged door – KEL 9206.600

Date : Jan 27, 2017

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Ex enclosures Plastic, empty enclosure with hinged door – KEL 9206.600

created: 27.01.2017 on www.rittal.com/com-en



Product description

Applications: Zone 1 and 2 or 21 and 22 to 94/9/EC
Ambient temperature range: -30°C...+80°C
The specified temperatures may be limited by the installed equipment
Protection type to EN 60 079: Equipment protection due to increased safety, equipment protection due to enclosure

Material: Fibre-glass-reinforced unsaturated polyester, surface resistance: $< 10^9 \Omega$
Door: Fibre-glass-reinforced unsaturated polyester, surface resistance: $< 10^9 \Omega$ all-round foamed-in silicone seal
Mounting plate: Sheet steel, zinc-plated

Colour: RAL 9011

**Protection category
IP to IEC 60 529:** IP 66

Certificates: IEC Ex PTB 10.0011U: yes
PTB 03 ATEX 1011U: yes

Supply includes: Enclosure
Door
Mounting plate

Basic material: Plastic

Product features

Dimensions: Width: 600 mm
Height: 600 mm
Depth: 200 mm

Mounting plate:	Width: 545 mm Height: 550 mm
Number of cam locks:	2
Lock version:	Cam
Number of locks:	2
Lock insert:	3 mm double-bit
Packs of:	1 pc(s).
Weight/pack:	15.9 kg
EAN:	4028177138360
Customs tariff number:	94037000
ETIM 6.0:	EC002503
ETIM 5.0:	EC002503
eCl@ss 8.0/8.1:	27180502
eCl@ss 7.0/7.1:	27180502
eCl@ss 6.0/6.1:	27180502
eCl@ss 5.1/5.1.4:	27180502
Approvals	
Approvals:	ATEX
Certificates:	EAC Ex Protection category
Declarations:	Manufacturer's declaration