



300mm x 18 Tpi - 5 pc

METAL: THIN KERF BLADES

- Improved tooth geometry for best speed and double the lifetime.
- Bi-metal quality cutting teeth with 8% cobalt giving the ultimate in performance and lifetime.
- TOUGH NECK™: Stamped indentations around the reception strengthens the blade at its weakest point.
- Slim 0.90 mm thick blade body optimised for maximum speed and flexibility.



Article Number	48475189
Blade length (mm)	300
Materials suited for	Thick metal > 4 mm Medium metal 1.5 - 4 mm Thin metal 0.5 - 3 mm Stainless steel Non ferrous metal (Cu/Al) PVC pipe
Max. cutting capacity metal pipe	ø 10 - 250
Max. cutting capacity non ferrous metals [mm]	1.5 - 8
Max. cutting capacity stainless steel [mm]	1.5 - 4
Max. cutting capacity steel (mm)	1.5 - 8