



Data sheet

ENGLISH

RS Stock No. 621-2388
RS Stock No. 621-2388



THERMOCOUPLES SHEATED WITH MINERAL INSULATION TYPE KNE HEAD

RANGE :

- 0°C / +700°C

USE:

- Universal

POINT FORT:

- Reagent, Strong

CARACTÉRISTIQUES :

- Thermocouple J type (Iron- Constantan)
- Hot junction undergrouded
- Sheath material : Alloy 600
- Mineral pressed Insulation
- Bendable
- KNE Head with small chain

DIMENSIONS:

- Sheath lenght = 200 mm
- Sheath diameter = 6 mm

DONNÉES MÉTROLOGIQUES:

- As per IEC 584
Standard tolerance TC "J" class1:
-40°C < t° < +125°C = ± 0,5°C
125°C < t° < +350°C = ± 0.004. [t]
- Time constant in water:- 20 sec
- Output signal FEM(mV) as per curve of J type as per norme IEC 60584

Other dimensions :

| Length | 400mm | 600mm |
|----------|----------|----------|
| Diameter | | |
| 6 mm | 621-2372 | 621-2394 |