

Endress+Hauser FTL325P-F1E1

Nivotester FTL325P



Level instrument, point level. Input: 1/3-channel, 2-wire PFM.

Picture for reference only. Product appearance may vary based on configuration

Configuration of FTL325P-F1E1:

Approval:	F	ATEX II (1)GD [Ex ia] IIC, WHG, IECEx [Ex ia] IIC
Housing:	1	Rail mounting, 22.5mm, 1-channel
Power Supply:	E	20-30VAC/20-60VDC
Switch Output:	1	1x SPDT level + 1x SPST alarm

Alternative part number: FTL325P-F1E1