

1571407-2 ✓ ACTIVE

Alcoswitch

TE Internal #: 1571407-2

Tactile Switches, Round Actuator Style, NO, Stainless Steel, Silver, Dust Proof, Low Profile, Support Bracket, 50 mA, 24 VDC, Process Sealed

[View on TE.com >](#)



Relays, Contactors & Switches > Switches > Tactile Switches



Actuator Style: **Round**

Operating Function: **NO**

Contact Base Material: **Stainless Steel**

Switch Contact Plating Material: **Silver**

Dust Proof: **Yes**

### Features

#### Product Type Features

Product Type	Switch
Leg Style	J Style
Illuminated	With
Actuator Style	Round
Dust Proof	Yes

#### Configuration Features

Tactile Feel	With
ESD Grounding Terminal	Without
Ganged	With
Tactile	Yes
Snap Action	Without
Operating Function	NO
Support Bracket	With
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	1

#### Electrical Characteristics

Tactile Switch Voltage Rating	24 VDC
-------------------------------	--------

#### Body Features



Case Color	Ivory
Actuator Force	260 g[9.178 oz]
Case Material	Thermoplastic (LCP)
Bushing Style	Unthreaded
Actuator Profile	Extended
Actuator Material	Silicone Rubber
Actuator Color	Black

### Contact Features

Contact Base Material	Stainless Steel
Switch Contact Plating Material	Silver
Tactile Switch Contact Current Rating	50 mA

### Termination Features

Termination Type	Printed Circuit Board
------------------	-----------------------

### Mechanical Attachment

Tactile Switch Mounting Type	Through Hole
Tactile Switch Mounting Angle	With

### Housing Features

Low Profile	With
Process Sealed	Yes

### Dimensions

Actuator Length	1.6 mm[.063 in]
Button Width	2.79 mm[.11 in]
	.236 in

### Usage Conditions

Temperature Rating	Standard °C
--------------------	-------------

### Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

### Other

Comment	(On) indicates momentary position.
---------	------------------------------------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 1825910-6  
FSM4JH=6MM TACT SWITCH, HIGH TEMP




TE Part # 2-1825910-7  
FSM14JH=6MM TACT SWITCH, HIGH TEMP




TE Part # 4-1437565-2  
FSM4JSMATR=TACT SWITCH 6X6MIL



TE Part # 3-1437565-0  
FSM2JSMATR=ON T/R



TE Part # 2-1977223-8  
FSM14JSMAS=6MM TACT SWITCH, SMT 160gf



TE Part # 1977497-1  
6MM SEALED R/A TACT SWITCH, SMT

### Customers Also Bought



TE Part #5788794-2  
25 HTMSFL PLUG RA 318 (IN,BL)



TE Part #9-1879210-1  
CPF 0402 1K27 0.1% 25PPM 5K RL



TE Part #2176337-5  
CRGCQ 0402 22R 1%



TE Part #1-2176337-8  
CRGCQ 0402 270R 1%



TE Part #2-2176350-5  
CRGCQ 2512 10K 5%




TE Part #2176350-7  
CRGCQ 2512 10R 5%



TE Part #3-2176370-7  
RQ 0603 1K02 0.1% 10PPM 5K RL



TE Part #641119-4  
04P MTA156 HDR ASSY FL/ST 15AU



TE Part #2-640504-2  
20P MR HDR ASSY VO LF



TE Part #AAD8410-00  
RW-175-1/16-X

## Documents

### Product Drawings

[R/A SEALED TACT SWITCH,T&R](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1571407-2\\_J.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1571407-2\\_J.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1571407-2\\_J.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages



[SWITCHES\\_CORE\\_PROGRAM\\_CATALOG](#)

English

[Products for Mobile Equipment](#)

English

---

[Product Environmental Compliance](#)

[TE Material Declaration](#)

English