

1846 Automatic cable reel, with 4Gx1.5 mm² cable

CE IP42

Features:

- 4Gx1.5 mm² cable
- Without thermal protection switch
- Cable length out of drum: 1 m
- Supplied without incoming cable
- Rack mechanism can be disabled to keep cable pulled
- Max. power (rolled up): 1400W (400V-20°C)
- Max. power (unrolled): 1900W (400V-20°C)
- Supplied with a 180° swivel bracket and an additional quick connection bracket



	art.	Cavo	L m	Scocca	
018460405	1846 10-H05	H05VV-F	10+1	A	4,4 kg
018460407	1846 10-H07	H07RN-F	10+1	A	5,2 kg
018460415	1846 15-H05	H05VV-F	15+1	A	5,4 kg

