

T8 FOOD GLASS LED TUBE

220-240V

LT1518FL

17,9 W - 1700lm - 3300K


IP 20

60.000 h

25.000



PF > 0,9



DIMENSIONS	A	B	C
1	1500	27	

GENERAL INFORMATIONS	
Code	LT1518FL
Ean	8031453022402
Family	T8 FOOD GLASS LED TUBE
Product line	LT
Technology	LED
Operating temperature (° C)	-20 - +50
Years warranty	5

LIGHTING DATA	
Light colour	076
CCT (K)	3300
Luminous flux (lm)	1700
Beam (°)	200
Luminous Efficacy (lm/W)	94,97

TECHNICAL FEATURES	
Base	G13
Power (W)	17,9
Supply voltage (V) / Max (V)	220 / 240
Power frequency (Hz)	50/60
Current consumption (mA)	88
Power factor	>0,90
Dimmer compatibility	NO
On/off cycles	25000
Nominal life (h)	60000

PACKAGING	
Packaging	BOX
Pack	10 / 10
Gross weight (Kg)	4.6
Net weight (Kg)	0.28

T8 FOOD GLASS LED TUBE
220-240V
LT1518FL
17,9W - 1700lm - 3300K

- Meat light tube - starter included
- Not compatible with electronic ballast

