













REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	INITIAL RELEASE	10APR2018	JA	DM
	H	REVISED PER E-20-007062	15MAY2020	EC	IG

1 CONTACT SIZE #4 2 CONTACTS SIZE #8 6 CONTACTS #12 SKT.  PIN  HDP24/HD34-24-9S MATES WITH HDP26/HD36-24-9P HDP26/HD36-24-9S MATES WITH HDP24/HD34-24-9P	1 CONTACT SIZE #4 1 CONTACT SIZE #12 12 CONTACTS SIZE #16 SKT.  PIN  HDP24/HD34-24-14S MATES WITH HDP26/HD36-24-14P HDP26/HD36-24-14S MATES WITH HDP24/HD34-24-14P	16 CONTACTS SIZE #12 SKT.  PIN  HDP24/HD34-24-16S MATES WITH HDP26/HD36-24-16P HDP26/HD36-24-16S MATES WITH HDP24/HD34-24-16P
1 CONTACT SIZE #8 3 CONTACTS SIZE #12 14 CONTACTS #16 SKT.  PIN  HDP24/HD34-24-18S MATES WITH HDP26/HD36-24-18P HDP26/HD36-24-18S MATES WITH HDP24/HD34-24-18P	6 CONTACTS SIZE #12 13 CONTACTS SIZE #16 SKT.  PIN  HDP24/HD34-24-19S MATES WITH HDP26/HD36-24-19P HDP26/HD36-24-19S MATES WITH HDP24/HD34-24-19P	4 CONTACTS SIZE #12 17 CONTACTS SIZE #16 SKT.  PIN  HDP24/HD34-24-21S MATES WITH HDP26/HD36-24-21P HDP26/HD36-24-21S MATES WITH HDP24/HD34-24-21P


4. PIN ID MARKINGS MUST BE VISIBLE FROM 6 INCHES AWAY IN NORMAL LIGHTING CONDITIONS.


3. ' / ' INDICATES EITHER, OR PART NUMBER.

2 SEALS WITH CAVITY SIZE #4 AND #8 ARE EXTENDED.

1. ALL VIEWS SHOW REAR END (GROMMET) OF CONNECTOR.

NOTES:




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. TOMSA 20NOV1995		 TE Connectivity								
DIMENSIONS: IN [mm]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK S. THEIS 04FEB1999		NAME ARRANGEMENT OF CONTACT LOCATION FOR HDP20 AND HD30 SERIES CONNECTORS SHELL SIZE 24								
		APVD R. REED 05FEB1999										
		PRODUCT SPEC										
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	APPLICATION SPEC		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO				
		WEIGHT		A 3		4AFU8	Ⓒ-0425-014-2400	-				
MATERIAL		FINISH		STANDARD SPECIFICATION				SCALE	SHEET	OF	REV	
								1 : 1	1	3	H	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

23 CONTACTS SIZE #16

SKT.




PIN




HDP24/HD34-24-23S MATES WITH HDP26/HD36-24-23P
HDP26/HD36-24-23S MATES WITH HDP24/HD34-24-23P

4 CONTACTS SIZE #12
19 CONTACTS SIZE #16
6 CONTACTS SIZE #20
THIS ARRANGEMENT IS FOR 'E' SEAL ONLY

SKT.




PIN




HDP24/HD34-24-29S MATES WITH HDP26/HD36-24-29P
HDP26/HD36-24-29S MATES WITH HDP24/HD34-24-29P

31 CONTACTS SIZE #16
THIS ARRANGEMENT IS FOR 'E' & 'T' SEAL ONLY

SKT.




PIN




HDP24/HD34-24-31S MATES WITH HDP26/HD36-24-31P
HDP26/HD36-24-31S MATES WITH HDP24/HD34-24-31P

33 CONTACTS SIZE #20

SKT.




PIN




HDP24/HD34-24-33S MATES WITH HDP26/HD36-24-33P
HDP26/HD36-24-33S MATES WITH HDP24/HD34-24-33P

3 CONTACTS SIZE #16
32 CONTACTS SIZE #20

SKT.




PIN




HDP24/HD34-24-35S MATES WITH HDP26/HD36-24-35P
HDP26/HD36-24-35S MATES WITH HDP24/HD34-24-35P

5 CONTACT SIZE #16
42 CONTACTS SIZE #20
THIS ARRANGEMENT IS FOR 'E' SEAL ONLY


SKT.







PIN




HDP24/HD34-24-47S MATES WITH HDP26/HD36-24-47P
HDP26/HD36-24-47S MATES WITH HDP24/HD34-24-47P

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. TOMSA	20NOV1995	TE Connectivity			
		CHK S. THEIS	04FEB1999				
		APVD R. REED	05FEB1999				
DIMENSIONS: IN [mm]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC		NAME ARRANGEMENT OF CONTACT LOCATION FOR HDP20 AND HD30 SERIES CONNECTORS SHELL SIZE 24			
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	APPLICATION SPEC					
MATERIAL	FINISH	WEIGHT					
		STANDARD SPECIFICATION		SIZE A3	CAGE CODE 4AFU8	DRAWING NO C-0425-014-2400	RESTRICTED TO -
				SCALE 1:1	SHEET 2 OF 3	REV H	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D	C	B	A	2 CONTACT SIZE #8 2 CONTACT SIZE #12 5 CONTACTS SIZE #16 SKT.  PIN  HDP24/HD34-24-91S MATES WITH HDP26/HD36-24-91P HDP26/HD36-24-91S MATES WITH HDP24/HD34-24-91P		
				3 CONTACT SIZE #4 4 CONTACT SIZE #16 SKT.  PIN  HDP24-24-7S MATES WITH HDP26-24-7P HDP26-24-7S MATES WITH HDP24-24-7P		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. TOMSA	20NOV1995	 TE Connectivity			
DIMENSIONS: IN [mm]		CHK S. THEIS	04FEB1999	NAME ARRANGEMENT OF CONTACT LOCATION FOR HDP20 AND HD30 SERIES CONNECTORS SHELL SIZE 24			
		APVD R. REED	05FEB1999				
		PRODUCT SPEC					
		APPLICATION SPEC					
		WEIGHT					
MATERIAL	FINISH	STANDARD SPECIFICATION		SIZE A3	CAGE CODE 4AFU8	DRAWING NO C-0425-014-2400	RESTRICTED TO -
				SCALE 1:1	SHEET 3	OF 3	REV H