

PRODUCT-DETAILS

332RAU6W

332RAU6W Panel mounted socket



General Information

Extended Product Type	332RAU6W
Product ID	2CMA166964R1000
EAN	7392696669641
Catalog Description	332RAU6W Panel mounted socket
Long Description	Socket-outlet, panel mounting, earthing sleeve position 6h, rated current 32A, IP67 watertight, unified flange, angled, 3-poles+earth, frequency 50-60 Hz, color code Red

Ordering

E-Number (Sweden)	E2416726
E-Number (Finland)	2421274
E-Number (Norway)	1561943
EAN	7392696669641
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	95 mm
Product Net Height	117 mm

Product Net Weight	0.21 kg
Mechanical Drawings	9AKK107991A3794

Container Information

Package Level 1 Width	112 mm
Package Level 1 Depth / Length	112 mm
Package Level 1 Height	139 mm
Package Level 1 Gross Weight	0.3 kg
Package Level 1 EAN	7392696669641
Package Level 1 Units	box 1 piece
Package Level 2 Width	800 mm
Package Level 2 Depth / Length	1200 mm
Package Level 2 Height	900 mm
Package Level 2 Gross Weight	125 kg
Package Level 2 EAN	7392696070812
Package Level 2 Units	pallet (lift) 350 piece

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1613211
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	3P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	2.5 ... 10 mm ²
Cable Diameter	13 ... 21.5 mm
Color	Red
Connection Type	Screw
Degree of Protection	IP67 IP69
Frequency (f)	50 Hz 60 Hz
Function	Socket outlet, panel mounting, unified flange, angled
Housing Material	Thermoplastic (PBT)

Invoice Description	Ind. P&S#332RAU6W
Mounting Holes	79.5x79.5
Mounting Type	unified flange, angled
Number of Poles	4
Order Multiple	1 piece
Product Main Type	TRAU
Product Name	Panel mounted socket
Protection Type	Watertight
Rated Current (I_n)	32 A
Rated Frequency (f)	50..60 Hz
Rated Voltage (U_r)	380 ... 415 V
Recommended Screw Driver	PH2
Standards	IEC 60309-1, -2
Suitable For	Socket Outlets for Panel Mounting
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700014C0016
RAL Number	RAL 7001 - Silver Grey

Classifications

eClass	27440504
UNSPSC	39120000

Technical

Wire Size	12 ... 10 AWG
Tightening Torque	WireClamp1.2 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Tough & Safe → Socket Outlets for Panel Mounting

