

PowerBreaker® H92M Metalclad **RCD Fused Spur**

The PowerBreaker Metalclad H92M RCD Fused Spur Unit gives added protection against the risk of electrocution by tripping if a leakage to earth is detected. It is suitable for use in areas where a spur outlet is required with RCD protection e.g. garages, workshops and where water is present, e.g. hand dryers in public areas.

- Complies with BS7288, BS1363
- Fuseholder with Securing screw
 - Padlock-off facility

TECHNICAL INFORMATION





DESCRIPTION H92

Voltage	230V AC~50Hz
Current rating	13A max
Rated trip current	30mA
Trip speed	<40mS
Cable capacity	6mm² max
Cable sheath diameter	8mm (maximum outside diameter)
Operating temperature	-5°C to +40°C
Compliance	BS 7288, BS 1363
Contact status indication	on/tripped by mechanical flag

PRODUCT REFERENCE:

Without neon H92MP-C With neon H92MN-C



