

## Protective covers - VC-SD-T3 - 1886744

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOCON protective cover for sleeve housing, with IP50 protection, type 3, max. tightening torque: 1.6 Nm

The illustration shows the version VC-SD-T4

### Why buy this product

- Easy mounting
- Contact inserts are protected when not plugged in



### Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 908430
Weight per Piece (excluding packing)	19.38 g
Custom tariff number	39269097
Country of origin	Poland
Note	Made to Order (non-returnable)

### Technical data

#### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 80 °C

#### General

Type	VC3
	For sleeve housing
Material	PA
Inflammability class according to UL 94	V0
Color	gray
Seal present	no

# Protective covers - VC-SD-T3 - 1886744

## Technical data

### General

Assembly instructions	Tightening torque 1.6 Nm
-----------------------	--------------------------

## Classifications

### eCl@ss

eCl@ss 4.0	27141210
eCl@ss 4.1	27141210
eCl@ss 5.0	27142104
eCl@ss 5.1	27142104
eCl@ss 6.0	27142104
eCl@ss 7.0	27142104
eCl@ss 8.0	27440208

### ETIM

ETIM 2.0	EC000241
ETIM 3.0	EC002040
ETIM 4.0	EC002040
ETIM 5.0	EC002314

### UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121712

## Drawings

Dimensioned drawing

