



Product number 1171253547
EAN 4007123685486

DESCRIPTION

- LED spotlight with super-bright Everlight SMD LEDs.
- Switch with light level function 100 % - 50 % - 25 %.
- Solid, modern aluminium housing.
- Stable, foldable frame with plastic protective corners and ergonomically shaped plastic carrying handle.
- Spotlight can be continuously swivelled and locked with one hand by means of a quick-release lock.
- Front screen made of safety glass.

TECHNICAL DATA

Cable quality	Rubber-Neoprene
Luminous flux	5800 lm
Power consumption	50 W
Luminous efficacy	144 lm/W
Energy efficiency class	A+ D
Colour rendering index	80-89 (class 1B)
Nominal input voltage	230 V

Min.-Max. Nominal input voltage	220 V - 240 V
Cable length	5 m
Cable designation	H07RN-F 3G1,0
With socket outlet	No
Impact strength	IK08
Protection class	I
Degree of protection (IP)	IP65
Colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1
Weight of product (without packaging)	1.96 kg
Dimension LxWxH (without packing)	7.5 cm x 27.5 cm x 26 cm

Weight of product (including packaging)	2.18 kg
Dimension LxWxH (incl. packing)	12.5 cm x 29.5 cm x 29 cm

SCOPE OF DELIVERY

LED Work Light JARO 7063 M