



### Main

|                             |               |
|-----------------------------|---------------|
| Range                       | OptiLine      |
| Product name                | OptiLine 45   |
| Cabling installation system | Pole          |
| Product type                | Pole          |
| Type of pole                | One-sided     |
| Pole/post surface finish    | Anodized      |
| Pole fixing mode            | Free-standing |

### Complementary

|                           |                    |
|---------------------------|--------------------|
| Colour                    | Natural            |
| Front opening size        | 45 mm              |
| Material                  | Aluminium anodized |
| Quantity package 1 / unit | Set of 1           |
| Height                    | 2450 mm            |
| Depth                     | 89 mm              |
| Width                     | 68 mm              |

### Environment

|                         |  |
|-------------------------|--|
| Standards               | 73/23/EEC<br>93/68/EEC<br>EN 50085-1:2005<br>EN 60598-2-2<br>IEC 1084-2-4<br>NF C 68-102<br>SS 424 10 32 |
| Operating temperature   | -25...60 °C  |
| IP degree of protection | IP30   |

### Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| RoHS exemption information | Yes  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |
| Circularity Profile        | No need of specific recycling operations   |