

Grease Gun LXT®

DGP180

18V • 410 g • 690 bar

Handy grease gun for lubrication applications

Practical grease gun which is ideal for lubrication applications for workshops, agriculture and heavy machinery. Capacity is 475 ml and the tool provides pressure of 69 Mpa. Light weight and compact in size which makes the tool nice to use. The tool features a hose with a length of 1.2 metres.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Max Pressure	690 bar
Hose length	1,2 m
Sound Pressure Level (L _{pA})	79 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Tool weight with battery	4,8 - 6,1 kg
Product Dimensions (L x W x H):	449 x 114 x 245 mm
Flow Rate	145 / 290 ml/min

User benefits

- Auto-switching mode for increased operability
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Variable speed control by trigger
- Lock-on feature for continuous operation



Related products

Optional AC

166094-6

Shoulder Belt

191A78-1

Adapter set

191F27-8

Cartridge Barrel C Set

191W61-0

Grease Gun Adapter Set (1pc)



1915N4-2

Lock On Adapter Set for Grease Gun



191F24-4

Cartridge barrel



191W60-2

Adapter set



821840-1

Plastic carrying case



Other

User manual

Parts drawing