



**Article Number:** 032901  
**Brady Material Number:** B-292  
**Brady Material Type:** Self-laminating Vinyl  
**Colour:** Yellow/Transparent  
**Order Reference:** WML-311-292-YL  
**Size - Height (mm):** 31.75  
**Size - Width (mm):** 25.40  
**Total Qty per Pack:** 250 Label / Roll  
**Printable Area - Height (mm):** 12.70  
**Printable Area - Width (mm):** 25.40

Overview      Specifications

## Specifications for ID Pro Plus, LS 2000 & BradyMarker XC Plus Printer Labels

<b>Adhesive Type</b>	Permanent Acrylic
<b>Application</b>	Wire & Cable Marking
<b>Approval/Compliance</b>	UL Recognised
<b>Article Number</b>	032901
<b>Brady Material Number</b>	B-292
<b>Brady Material Type</b>	Self-laminating Vinyl
<b>Colour</b>	Yellow/Transparent
<b>Finish</b>	Matt
<b>Long Description</b>	Printable, self-laminating vinyl labels for the ID Pro® Plus, LS 2000™ & BradyMarker™ XC Plus printers. This material is UL Recognized to UL969 Labeling and Marking Standard when printed with the Brady Series 2000™, 5000™, and 7300™ dot matrix ribbons. See UL files MH10939 for specific details.
<b>Max. Characters per Line</b>	Large - ID Pro: 7, LS 2000: 7, Small - ID Pro: 10, LS 2000: 15
<b>Max. Lines of Text</b>	ID Pro: 3, LS 2000: 4
<b>Max. Service Temp. °C</b>	70
<b>Max. Wire/Cable Diameter (mm)</b>	6.00
<b>Order Reference</b>	WML-311-292-YL
<b>Printable Area - Height (mm)</b>	12.70

<b>Printer Compatibility</b>	IDPro; LS2000; BMXC
<b>Ribbon Series</b>	R5000
<b>Size - Height (mm)</b>	31.75
<b>Size - Width (mm)</b>	25.40
<b>Special Properties</b>	Self-extinguishing;Self-laminating
<b>Total Qty per Pack</b>	250 Label / Roll
<b>Industry</b>	Data & Telecommunications;Electrical
<b>Min. Service Temp. °C</b>	-40
<b>Printable Area - Width (mm)</b>	25.40
<b>QTY. per Row</b>	1
<b>Thickness (mm)</b>	0.102