


CROSS LASER LEVEL + 5 POINTS - GREEN BEAMS - USB-C

USB-C charging with built-in Li-ion batteries
Li-ion batteries with POWERSTACK technology™
Minimum autonomy of 8 hours
USB-C cable charging: 80% charge in 30 minutes (45W PD)
The laser can be used when loading



VERY EFFICIENT

- High visibility diodes for a very clear visibility of the beams
- Accuracy +/- 3 mm at 10 m
- 30 M / 100 M with detection cell

PRECISE

Fine alignment screw for simple and quick positioning of the beam on the user's markers

PRACTICE

Indicator of the battery level to know if need recharge at a glance

ADAPTS TO THE CONDITIONS OF THE SITE

With 3 light intensity adjustments of the beams to gain autonomy or to refine the beam according to the nature of the support material (stainless steel...)

IS FIXED ANYWHERE

- Easy grip with very powerful swivel magnetic mount
- Built-in tripod thread of 1/4" and 5/8"

VERSATILE

Button easy change of modes between manual slope / self-leveling / pendulum blocking

RESISTANT

- Windows mounted on a rubber support seal
- IP65 (dust and low pressure water jet)
- Test fall 1 m
- Battery protected in the base in polycarbonate GF10 (very resistant and stable temperature and UV)



Delivered with compact soft case, wall bracket, USB-C cable.
Plug not included

DCLE14251GB-XJ

5 035 048 810 811