



Vertical busbar support non-cascaded, W: 200 mm, 1 set = 3 units

Model	
product brand name	SIVACON S4
product designation	Vertical busbar holder non-cascaded
design of the product	width 200
General technical data	
number of poles	4
Main circuit	
operational current rated value maximum	2 810 A
type of connectable conductor cross-sections for copper conductor stranded	20x10, 30x10, 40x10, 50x10
Mechanical Design	
height	155 mm
width	340 mm
depth	30 mm
busbar center-to-center spacing	80 mm
net weight	5 000 g
Approvals Certificates	
General Product Approval	other



[Miscellaneous](#)



[Miscellaneous](#)

other	Environment
Confirmation	Environmental Con- firmations
	Environmental Con- firmations

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875
Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ4000-0BA77
Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/8PQ4000-0BA77
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ4000-0BA77

last modified:

4/4/2025 

