



ENGLISH

Datasheet

# RS Pro 100W E40 LED 360 Corn Lamp

RS Stock No:184-6996



This RS Pro 100W E40 IP65 rated LED Corn Lamp, is ideally suited for commercial applications such as warehouses and factories. Compatible for use with PIR sensors and fits many different fixtures as a replacement for traditional lamps. Larger heat sink enables production without a fan and a long lifespan rated at 50,000 hours.

## Typical Properties

ENGLISH

Material	Aluminium Body/PC Diffuser
Wattage	100W
Supply Voltage	100 – 240 50/60Hz
Power Factor	≥0.9
Colour Temperature	6500k
Colour Accuracy (CRI)	≥80
Lumens	14,000lm
Luminous Efficiency	140lm/W
Beam Angle	360°
Product Colour	White
Replaceable LED's	No
Dimmable	Yes
IP Rating	IP65
Rated Life	50,000 Hours

