



Part Number : [747572301](#)

Product Description : QSFP-to-QSFP Cable
Assembly, 28 AWG, 3.0m Length

Series Number : 74757

Status : Obsolete

Product Category : High-Speed I/O Cable
Assemblies



Documents & Resources

Specifications

[TS-74757-0011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains C,C'-azodi(formamide) per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	High-Speed I/O Cable Assemblies
Series	74757
Description	QSFP-to-QSFP Cable Assembly, 28 AWG, 3.0m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	QSFP-to-QSFP
Product Name	QSFP
UPC	800756775395

Agency

UL	E72548
----	--------

Electrical

Impedance	100Ω
-----------	------

Physical

Cable Length	3.0m
Circuits (Loaded)	MSA
Gender	Plug
Lock to Mating Part	Yes
Net Weight	244.000/g
Single Ended	No
Wire/Cable Type	Round
Wire Size (AWG)	28

Mates With / Use With

Mates with Part(s)

Description	Part Number
iPass I/O Right-Angle Surface Mount Receptacles	<u>75586</u>

Use with Part(s)

Description	Part Number
QSFP+ Cage Assemblies, Light Pipes, and Heat Sinks	<u>74750</u>
QSFP+ 1x3 Ganged Cage Assemblies and Heat Sink Clips	<u>74768</u>
QSFP+ Ganged Cages and Light Pipe Assemblies	<u>74769</u>