



FLAMESTAT HIGH VIS STRETCH TROUSERS CLASS 2 2161 ATHF

ART. NO: 129517

Stretch material / Dirt, oil and water repellent / Concealed front button / 2 front pockets / 2 reinforced back pockets with flap and concealed snap fastening / Double reinforced crotch seam / Reinforced pocket for folding rule and tools with flap and concealed snap fastening, pen holder and button and loop for sheath knife / Leg pocket with flap and concealed snap fastening, mobile phone pocket and loop for ID-card holder / Reinforced knee pockets with inside opening / Height adjustment for kneepad pads in knee pocket / Metal free / Approved according to EN 61482-1-2 APC 1, EN 61482-1-1 ELIM: 8 cal/cm² (included in electric arc certified garment combinations), EN ISO 11612 A1 B1 C1 F1, EN 1149-5, EN ISO 11611 A1 class 1 (included in flame and welding garment combinations), EN 13034 Type PB [6], EN ISO 20471 class 2 and EN 14404 together with kneepads 124292 / Certified after 50 washes / Leasing laundry-tested according to ISO 15797 / OEKO-TEX® certified.

Material: Stretch 45% modacrylic, 34% cotton, 17% polyamide, 2% elastane, 2% anti-static fibre. Reinforcement 45% modacrylic, 35% cotton, 18% polyamide, 2% anti-static fibre. Inherent flame protection. In transition to PFAS free.

Weight: Stretch 265 g/m². Reinforcement 300 g/m².

Color: F171 High vis Yellow/Navy

Size: Tall: C146-C156 Regular: C44-C62 Short: D84-D116



EN 11612



EN 11611



EN 1149-5



IEC 61482-2



EN 13034



EN 20471



EN 14404



FRISTADS®

SIZES MAY VARY BETWEEN COLORS
Print date: 2025-09-04