Product datasheet
Characteristics

NSYCVF38M230PF

ClimaSys forced vent. IP54, 38m3/h, 230V, with outlet grille and filter G2

Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Type of ventilation filter	Standard
Air flow	Free flow rate with standard filter : 39 m3/h at 60 Hz Free flow rate with standard filter : 38 m3/h at 50 Hz
[Us] rated supply voltage	150...250 V
Input voltage	230 V 50/60 Hz

Complementary

Rated power in W	4.5 W 50 Hz 4.8 W 60 Hz
[In] rated current	0.16 A 50 Hz 0.17 A 60 Hz
Noise level	40...41 dB
Bearing type	Ball
Height	External : 137 mm
Width	External : 117 mm
Depth	External : 49 mm
Cut-out dimensions	92 x 92 mm
Product weight	0.22 kg
Material	Injected thermoplastic (ASA PC) for outlet grille
Colour	Outlet grille : grey RAL 7035
Ambient air temperature for operation	-10...70 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	29 Pa flow rate 0 m³/h
Connections - terminals	Cable
IP degree of protection	IP54
Device composition	1 outlet grille front 1 axial motor 2 protective grille on the front and rear surfaces 1 filter front of axial motor 1 cut-out template
Condition of use	Outside temperature must be 5 °C lower than inside temperature Filter must be cleaned and replaced regularly Surrounding environment must be relatively clean Overfrequent filter replacement should be avoided Flow rates depends on the work point, see ProClima software
Installed device	-MUST NOT be connected to a power conversion module, an inverter or UPS type of power supply

Environment

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty period	18 months