

Retaining plate Han-Eco Modular M32



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 000 9941
Specification	Retaining plate Han-Eco Modular M32
HARTING eCatalogue	https://harting.com/19410009941

Identification

Category	Accessories
Series of hoods/housings	Han-Eco® Modular
Type of accessory	Retaining plate

Technical characteristics

Limiting temperature	-20 ... +125 °C
Ambient temperature	-20 ... +50 °C

Material properties

Material (accessories)	Polyamide (PA)
Colour (accessories)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	50
Net weight	2.68 g
Country of origin	Please contact your local HARTING subsidiary.



Pushing Performance
Since 1945

Commercial data

European customs tariff number	85366990
GTIN	5713140830486
eCl@ss	27440392 Connector (accessories)
ETIM	EC002939
UNSPSC 24.0	39121400