

## ML5520/ML5521 DOT MATRIX PRINTER



- ❖ ML5520
- ❖ ML5521
- ❖ 9-PIN DOT MATRIX PRINTER

### **HIGH PERFORMANCE, VERSATILE PRINTER FOR DEDICATED FORMS PRINTING**

The ML5520/ML5521 narrow and wide carriage printers offer true flexibility making them ideal for practically any application. Engineered for productivity, the ML5500 Series also has the levels of reliability synonymous with the Microline range. In short, versatility and robustness to meet your print requirements in the most demanding of work environments.

### **MAIN FEATURES OF THE ML5520/ML5521 PRINTER**

- ❖ Oki reliability backed by 20,000H MTBF
- ❖ Optimised for high levels of throughput
- ❖ Integrated USB and IEEE Parallel Standard Interfaces
- ❖ Multi-copy capability (up to 6-part forms)
- ❖ Up to 570cps Super Speed Draft
- ❖ 128KB Buffer memory
- ❖ Low noise (56dB(A) in standard operation and 52dB(A) in quiet mode)



# OKI

# ML5520/ML5521 DOT MATRIX PRINTER

## PRODUCT SPECIFICATION

		ML5520	ML5521
<b>General</b>	Number of pins	9	
	No. of multi-part forms	6 (one original + 5 copies)	
<b>Speed &amp; throughput</b>	Super speed (12cpi)	570cps	
	High speed draft (10cpi)	507cps	
	Utility	380cps	
	Near letter quality	95cps	
	Fastest print speed	570cps	
<b>Font &amp; print features</b>	Carriage width (10cpi)	80 columns	136 columns
	Max. in compressed mode	160 columns	272 columns
	Character pitch	10/12/15/17.1/20 pitch & proportional	
	Graphics resolution	Up to 240 x 216 dpi	
	Typeface & Font	NLQ-Courier (Scalable), NLQ-Gothic (Scalable), OCR-B, High Speed Draft, Utility + Barcodes	
	Typestyle	Emphasised, Enhanced, Double Width, Double Height, Italics, Bold, Superscript, Subscript, Underline, Overscore	
<b>Emulations &amp; interfaces</b>	Printer emulations	Epson FX, IBM ProPrinter, Oki Microline	
	Standard interfaces	Centronics Parallel + USB	
	Optional interfaces	Serial RS 232C/RS 422/Current Loop	
<b>Paper-handling</b>	Continuous paper	76–254mm	76–406mm
	Continuous envelopes	165 x 92mm	241 x 105mm
	First printable line (from top of page)	Cut-sheet: 0.5mm Continuous: 0.5mm	
	Standard	Paper parking, Low tear-off, Push tractors, Autoload single sheet	
	Optional	Pull tractor, Single/dual bin sheet feeder, Roll paper stand (80 column only), Bottom Push tractor	
<b>Physical</b>	Dimensions (HxWxD)	153 x 398 x 345mm	153 x 552 x 345mm
	Weight	7.5kg	9.5kg
	Memory	128KB	
	Noise level	56dB(A) normal operation / 52dB(A) in quiet mode	
<b>Power</b>	Power requirements	230V AC	
	Frequency	50/60Hz	
<b>Reliability</b>	Print head life	200 million characters	
	Ribbon life	4 million characters (re-inking cartridge)	

# OKI

Only use genuine Oki Original consumables to ensure the best quality and performance from your hardware. Non Oki Original products may damage your printer's performance and invalidate your warranty. Specifications subject to change without notice. All trademarks acknowledged.

Oki, Network Solutions  
for a Global Society

OKI EUROPE, PART OF OKI ELECTRIC

OKI EUROPE LTD,  
CENTRAL HOUSE, BALFOUR ROAD,  
HOUNSLOW, MIDDLESEX, TW3 1HY,  
UNITED KINGDOM  
TEL: +44 (0)20 8219 2190  
FAX: +44 (0)20 8219 2199  
[WWW.OKIEUROPE.COM](http://WWW.OKIEUROPE.COM)



As an ENERGY STAR Partner, Oki Europe Ltd has determined that this product meets the ENERGY STAR guidelines for energy efficiency

©2003 Oki Europe Ltd.