

**ARCANOL-MULTI3-5KG** [↗](#)

Bearing grease

Multi-purpose grease ARCANOL-MULTI3

Technical information

Your current product variant

| | | |
|-----------------|------|-----------------------|
| Grease category | MP | Multi-purpose greases |
| Package size | 5 KG | 5 kg bucket |

Technical data

| | | |
|----------------------|-------------------------|------------------------------------|
| $\vartheta_{O \min}$ | -30 °C | Operating temperature, min. |
| $\vartheta_{O \max}$ | 120 °C | Operating temperature, max. |
| ϑ_G | 75 °C | Upper continuous limit temperature |
| $n \cdot d_M$ | 500.000 mm/min | Speed of rotation specific value |
| | Lithium soap | Thickener type |
| | Mineral oil | Base oil type |
| ν_{40} | 110 mm ² /s | Base oil viscosity at +40°C |
| ν_{100} | 12 mm ² /s | Base oil viscosity at +100 °C |
| | 3 | NLGI class |
| | Multi-purpose grease | Grease category |
| ρ | 0,95 kg/dm ³ | Density |
| | 5 kg bucket | Container |
| $\approx m$ | 5,4 kg | Weight |