

# PERFORMANCE GROUND POINT HSS 19PC DRILL SET



## P-19906

Description: 19 Pc Performance HSS bit set

Pack Quantity: 19

Diameter (D): 1-10mm



NO IMAGE  
AVAILABLE

- These bits have a 118° ground point for fast and accurate drilling.
- Star Rating: \*\*\*\*
- Sub-brand: Performance Ground Point HSS
- Application: Steel, Cast iron, aluminium, brass, copper, non-ferrous, wood, engineering, automotive as well as mild steel and wood.
- Features: 118 degree ground point. Milled Body. Helicoidal Flute. DIN338RN. 19 piece set, supplied ins steel case.
- Contains: 19 - HSS Groundpoint Bits, Sizes: 1,1.5,2,2.5,3,3.5,4,4.5,5,5.5,6,6.5,7,7.5,8,8.5,9,9.5mm.
- They are milled from a solid steel form which means a higher level of strength and preciseness.
- Helicoidal Flute to improve swarf discharge.