



TWIN 18V TOP HANDLE CHAIN SAW BL LXT

DUC306Z

These models are cordless top handle chain saws powered by 18Vx2 LXT Li-Ion batteries in series, providing excellent cutting performance equivalent to 30cc class engine chain saws.

To be used by trained tree surgeons only!



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	36 (18v x2) v
Chain Gauge	0.043 "
Chain Pitch	3/8 "
Chain Speed	0 - 20 m/sec
Bar Size	30 cm
Noise sound pressure	89 dB(A)
Noise sound power	103 dB(A)
Noise K factor	3 dB(A)
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Wood	3.2 m/sec ²
Net weight	4.6 – 5.1 kg

USER BENEFITS

- Captive nuts: prevent loss of nut when removing sprocket cover to replace guide bar or saw chain
- Brushless motor
- Variable speed control by trigger
- Electric chain brake
- Kickback brake
- Oil Capacity Display
- Powered by two 18V Li-ion batteries in series to supply energy to the powerful 36V DC motor drive system.
- Main power switch with auto power-off function
- Hook located to position the guide bar straight down when the chain saw hangs from user's waist
- Metal spike bumper: Firmly grips workpiece to provide more control, making cutting easier.
- Torque boost mode: raises the current limit temporarily for faster cutting of thicker branches

[Link to product - makitauk.com](https://makitauk.com)



RELATED PRODUCTS

(Recom

■ OTHER