



Datasheet

Stock No: 315-1218

ENGLISH

RS Pro Red LED Lighting Bulkhead, 24 V ac/V dc, IP64, with Red Diffuser



Product Details:

Long Life LED Bulkhead

- Designed to replace GLS red bulkheads
- 90,000 hr, 3000mcd LED's
- Wide operating temperature range
- Fitted with a high impact red polycarbonate diffuser
- Bases have 20mm conduit knockouts for side and bottom cable entry

Supplied with: security screws



Specifications:

Voltage Rating:	24 V ac/V dc
Lamp Type:	LED
Lamp Supplied:	Yes
Diffuser Colour:	Red
Light Output Colour:	Red
Length:	245 mm
Width:	112 mm
Depth:	125 mm
Dimensions:	245 x 112 x 125 mm
Lamp Shape:	Rectangular
Maximum Operating Temperature:	+85°C
Minimum Operating Temperature:	-20°C
IP Rating:	IP64
Operating Temperature Range:	-20 → +85°C