



Technical data

NUTR204X/3AS

Roller follower with inner ring

Needle roller bearing, roller follower, full-complement cylindrical roller, with inner ring, double-side shields, cylindrical outer ring

PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	20 mm
D - External diameter	47 mm
C - Width of bearing, drawn cup or outer ring	24 mm
F - Under roller diameter	25,5 mm
B - Bearing/Inner ring width	25 mm
e - Inlet diameter of roller or washer	27 mm
rs - Min fillet radius	0,3 mm
Bearing with/without cage	Sans
Radial clearance class	CN
Precision class	P0
Mass	0,245 kg

PRODUCT PERFORMANCE

Cr - Dynamic load rating	38500000 mN
C0r - Static load rating	48000000 mN
Track load capacity cylindrical outer ring	21000000 mN
N lim - Grease lubrication limit speed	24000 °/s
Tmin - Min operating temperature	253,15 °K



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT PERFORMANCE

Tmax - Max operating temperature

393,15 °K

