

STANLEY

STANLEY FATMAX® 10 Piece Parallel/Phillips/Pozi VDE Screwdriver Set

5-62-573



Features:

- Parallel 2.5mm X 50mm, 3.5mm X 75mm, 5.5mm X 150mm
- Phillips PH0 X 75mm, PH1 X 100mm, PH2 X 125mm
- Pozi PZ0 X 75mm, PZ1 X 100mm, PZ2 X 125mm
- Voltage Tester

Description:

The STANLEY FATMAX® 10 Piece Parallel/Phillips/Pozi VDE Screwdriver Set has been constructed using chrome vanadium steel, the hardened tip allows for high torque and reduces the chances of tip breakage, leading to a longer tool life. The heavy duty plastic sheath running the length of the bar protects the user from live current. All STANLEY VDE screwdrivers are individually tested to 10,000 volts, and guaranteed to protect against 1,000 volts. Red handles help self selection and identification of a VDE screwdriver. The handle design has been moulded to the bar creating a virtually unbreakable bond that is highly durable.

Specifications	
Colour	Red/ Yellow
Bar Material	Chrome Vanadium
Quantity	10