

LED RECHARGEABLE TACTICAL FLASHLIGHT

Product Specifications

SPECIFICATIONS	OBS-IM3 / OBS-IM3-G
Color	Black/Red
Material	Aluminum
Luminosity (Lumen)	1500 (Turbo Mode) 1200 (High Mode) 600 (Medium Mode) 20 (Ultra-Low Mode)
Rechargeable	Yes
Battery Type	Lithium-Ion or AAA (3)
Runtime	30s (Turbo Mode) 3h (High Mode) 8h (Medium Mode) 72h (Ultra-Low Mode)
Charge Time	3.5h
Charging Port	USB-C
Power Bank for Charging Phones	Yes (5V, 1A)
Weight	7.6 oz / 215 g
Length	6.9 in / 176 mm
Width	1.3 in / 34 mm
Height	1.3 in / 34 mm
Storage/Operating Temperature	+15°F to +120°F / -10°C to +50°C
IP Rating	IP65
IK Rating	IK07
Zoom	Yes
Magnet	Yes
Accessories	Clip, 3in1 Charging Cable(Apple Lightning, micro-USB, USB Type-C), AAA Battery Holder