

FEATURES

- **Sintered Bronze Material:** Offers excellent wear resistance and durability, ideal for demanding environments.
- **1.25 in Inside Diameter:** Ensures compatibility with a wide range of shafts and components.
- **2.99 in Outside Diameter:** Provides a large contact area for effective load distribution.
- **0.25 in Thickness:** Delivers optimal strength while maintaining a compact profile.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with varying loads, ensuring consistent performance.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads, enhancing system reliability.
- **ISO 9001:2008, UKAS 001 Approved:** Meets international quality standards for assured performance and safety.

RS PRO Sintered Bronze Thrust Washer, 1.25 in ID

RS Stock No: 518-149



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

Product Description

This RS PRO sintered bronze thrust washer is designed to provide reliable performance in high-load applications. With its robust construction, it ensures efficient load distribution and reduces friction between moving parts, enhancing the longevity of mechanical systems.

General Specifications

Dynamic Load Rating	14 N/mm ²
Product Type	Thrust Washer
Static Load Rating	50 N/mm ²
Sub Type	Washer

Mechanical Specifications

Inside Diameter	1.25 in
Material	Sintered Bronze
Outside Diameter	2.99 in
Thickness	0.25 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

