

Polyurethane General Use Tubing, Standard Inch Size - TIUB TIUB11R-20

Datasheet

General series information

- Applicable tubing O.D.: 1/8" to 1/2"
- Operating temperature: -20 to 60 °C for air and 0 to 40 °C for water
- 29 colour variation.

Standard specifications

Size	11 (ODØ9.53, IDØ6.35)
Color	R (Red)
Roll Length	20 m
Reel Length	None
Suffix	None
Pressure medium	Air, Water
Maximum operating pressure	0.8 MPa
Maximum ambient temperature	60 °C / 40 °C for Water
Minimum ambient temperature	-20 °C (with no freezing) / 0 °C for Water
Weight	0.962 Kg

Additional information

Catalogue

[TU-29COLOR-A_EU.pdf](#)