


Pneum. contact metal ID 4 male



Part number	09 14 000 6304
Specification	Pneum. contact metal ID 4 male
HARTING eCatalogue	https://b2b.harting.com/09140006304

Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	Without shut-off Straight

Version

Gender	Male
--------	------

Technical characteristics

Limiting temperature	-20 ... +85 °C
Operating pressure	≤10 bar
Tube inner diameter	4 mm

Material properties

Material (contacts)	Brass
Material (seal)	NBR
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes



Pushing Performance

Material properties

REACH SVHC substances Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	10
Net weight	10.9 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27440204 Contact for industrial connectors