



Brand of NTN corporation

Technical data

UCFLE207

Bearing units




Grey cast housing, radial insert ball bearing with socket set screws, seal with slinger

KIT CONTENT

UC207G2, FLE207

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
A - Housing height	33,7 mm
A1 - Housing foot height / flange height	12,5 mm
A2 - Total height from mounting surface	46,4 mm
B - Width of Inner Ring	42,9 mm
d - Shaft diameter	35 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

e - Distance mounting surface to bearing center	21 mm
G - Grease fitting	R1/8"
H - Housing length, width or diameter	155 mm
J - Mounting holes distance	130 mm
L - Housing width / diameter	92 mm
N - Mounting hole dimension	14 mm
S - Distance front side/bearing centre	17,5 mm

PRODUCT PERFORMANCE

C - Dynamic load rating	25700000 mN
C0 - Static load rating	15200000 mN
Operating temperature min.	253,15 °K
Operating temperature max.	373,15 °K

OTHER FEATURES

Mass	1,17 kg
Recommended tightening torque for set screw	11.5 N-m

