



182.72.104.66GYE...KRR-B Spannlager

Radial insert ball bearings GYE45-XL-KRR-B (Series GYE...KRR-B)

spherical outer ring, location by grub screws, R seals on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	45 mm
DSF	85 mm
B	49,2 mm
A	8 mm
C	22 mm
C2	26,4 mm
Ca	6,4 mm
D1	72,3 mm
d1	57 mm
S	19 mm
W	4 mm
m	0,71 kg Mass
Cr	34500 N Basic dynamic load rating, radial
Cor	20400 N Basic static load rating, radial
Cur	1030 N Fatigue limit load, radial
fo	14,3 Calculation factor

