



Cut



Heat



Medium Duty

Durable, versatile cut-resistant gloves, specially designed for demanding applications

- **Enhanced protection:** Featuring INTERCEPT™ Cut Resistance Technology, these nitrile-coated gloves meet ANSI/ISEA 105-2024 CUT A7 and EN ISO F standards, ensuring improved workplace safety
- **Assured heat resistance:** HyFlex® 11-543 industrial safety gloves satisfy EN 407 contact heat level 1 requirements, enabling them to withstand heat up to 100°C/212°F for at least 15 seconds
- **Improved durability:** Featuring FORTIX™ Abrasion Resistance Technology, these HyFlex gloves offer excellent abrasion resistance than the previous generation, with a dirt-masking design further extending glove life
- **Reduced surface defect risks:** HyFlex® 11-543 industrial work gloves are also silicone-free, preventing contaminant transfer to metal before painting



Industries

- Automotive
- Glass manufacturing
- Machinery and Equipment
- Metal fabrication

Applications

- Heavy final assembly
- Machining
- Grinding
- Maintenance
- Material handling
- Primary assembly
- Stamping
- Compatible with consumer and industrial touchscreens

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-543

Lightweight high cut protection
featuring INTERCEPT™ Cut Resistance
Technology

Key Features

- **INTERCEPT™ Technology:** ANSI/ISEA 105-2024 CUT A7 and EN ISO F
- **FORTIX™ Technology:** Excellent abrasion resistance
- **EN 407 contact heat level 1:** Hand protection up to 100°C/212°F

Technologies



FORTIX™

Abrasion Resistance Technology



INTERCEPT™

Cut Resistance Technology



Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN 388



4X32F

EN388: 2016



4X32F

EN 407



X1XXXX

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-543	Finishing: Palm Coated Coating Material: Nitrile Liner Material: Stainless steel, HPPE, Nylon, Spandex Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	213-267MM; 8.4-10.5 INCHES	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell