



6-569278-2 | MP-5EU-5
Modular Plug, 8P/8C, Unshielded, Round, 500 pcs

Body Features

Conductor Type Solid | Stranded

Configuration Features

Number of Positions 8
Keyed No

Contact Features

Contact Base Material Phosphor bronze
Contact Mating Area Plating Material Gold
Contact Mating Area Plating Thickness 50.00 μin | 1.27 μm
Number of Contacts Loaded 8

Dimensions

Cable Jacket Outside Diameter Range 0.190–0.220 in | 4.8–5.6 mm
Conductor Outside Diameter 0.034–0.039 in | 0.86–0.99 mm
Conductor Wire Size 26–23 AWG

Housing Features

Housing Material Glass filled polycarbonate

Industry Standards

UL Flammability Rating UL 1863

Packaging Features

Packaging Quantity 500

Product Availability

Region Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Features

Cable Type Round, unshielded
Performance Category Category 5e
Connector Style Plug
Jack Type RJ45
Latch Style Standard

6-569278-2 | MP-5EU-5

Product Type	Connector
Shielded	No

Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
----------------------------------	-------------------------------------