

Professionally approved products.

Datasheet

Crimp Tool for Open barrel connectors

RS Stock number: 683-1611



Specifications:

- Non slip main handle and low friction moving handle ensure a comfortable hand grip
- Provides two-hand grip in the final phase of crimping, increasing comfort and productivity
- Full cycle crimp mechanism to ensure consistent, reliable crimp
- Ratchet release mechanism to clear miss-crimps and obstructions
- Precision eccentric adjustment for consistent performance and ability to calibrate
- Each tool has a unique serial number for traceability
- Durable: life span exceeds 50,000 cycles
- High strength, through hardened alloy Swedish steel construction

Crimp nest: 0.5-1.5 mm² / AWG 20-16
 1.5-2.5 mm² / AWG 26-14
 4.0-6.0 mm² / AWG 12-10

Wire size: 0.5-6.0 mm² / AWG 22-10

Connector: Non insulated / Uninsulated Open barrel / Receptacle connectors

Description: For uninsulated open barrel connectors

Crimp profile: B/F-crimps

Length: 225 mm/8.86"

Width: 21 mm/0.83"

Height: 70 mm/2.76"

Weight: 540 gr/1.19 lb

Life span, cycles: 225 mm/8.86"