



Datasheet

Stock No: 313-6297

ENGLISH

RS Pro Beige, Grey Polypropylene (PP) Rod, 1000mm x 20mm Diameter



Product Details:

Polypropylene Beige/Grey

- Low density combined with hardness, stiffness, tensile strength and fatigue resistance
- Good chemical resistance
- Typically used for plugs, pallets, filter parts, pump parts and in chemical plant construction
- Beige/Grey in colour

Max. Service Temperature (Long Term) °C	100°C
Elongation at Break	65%
Tensile Strength (MPa)	35
Hardness	80 MPa (DIN ASTM Ball Indentation)
Flammability Rating	UL 94 HB
Water Absorption (%)	0.03



Specifications:

Colour:	Beige, Grey
Length:	1000mm
Material:	Polypropylene
Form:	Rod
Rod Diameter:	20mm
Tensile Strength:	35 MPa
Flammability Rating:	UL 94 HB
Elongation:	65%
Hardness:	80 Ball Indentation
Maximum Operating Temperature:	+100°C
Water Absorption:	0.03%