

Features

- EN No 10/2011
Compliant for food
contact applications.
- Lightweight for easy
handling.
- Transparent for easy
visibility.
- Remains flexible,
even in colder
conditions.
- Excellent chemical
and abrasion
resistance.
- NSF51 + NSF61
approved for the
transfer of drinking
water.
- RoHS 3 compliant.
- Manufactured with a
white rigid crush and
kink resistant anti-
shock PVC spiral helix
encapsulated in a
transparent flexible
FDA approved PVC
cover, with a smooth
inside wall.

RS PRO Hose Pipes & Flex Tubes

RS Stock No.: 0336812



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A lightweight clear non-toxic PVC delivery hose, manufactured from EC compliant materials, suitable for food delivery applications. Reinforced with a rigid crush and kink resistant white PVC helix, this hose is tough, flexible and extremely durable even under cold working conditions. It has outstanding resistance to the effects of weather and minimum frictional loss is achieved by the smooth bore. This is a highly flexible hose designed for low pressure suction and delivery of liquids and light powders.

Key Features:

- EN No 10/2011 Compliant for food contact applications.
- Lightweight for easy handling.
- Transparent for easy visibility.
- Remains flexible, even in colder conditions.
- Excellent chemical and abrasion resistance.
- NSF51 + NSF61 approved for the transfer of drinking water.
- RoHS 3 compliant.

Construction:

Manufactured with a white rigid crush and kink resistant anti-shock PVC spiral helix encapsulated in a transparent flexible FDA approved PVC cover, with a smooth inside wall.

Applications:

- Food industry

General Specifications

Hose Pipe / Flexible Tube	Flexible Tube
Colour	Clear
Features	Reinforced
Series	RS PRO FDH
Inner Diameter	38mm
Outer Diameter	45.4mm
Material	PVC
Hose Pipe Action	Transfer, Vacuum
Maximum Working Pressure	6.5bar
Suitable Application	Beverage, Food
Minimum Operating Temperature	-10°C
Maximum Operating Temperature	+80°C
Length	30m
Reinforced	Yes
Bend Radius	171mm
Standards Met	NSF 51, NSF 61