

Cable connection 3VA12 (250 A), fixed-mounted, plug-in socket, withdrawable, H: 150 mm



Model	
product brand name	SIVACON S4
product designation	3VA connection front
design of the product	3VA12 (up to 250 A)
design of the surface	zinc plated
General technical data	
design of pole	3
design	assembly kit
suitability for use	for 3VA molded-case circuit breakers
RAL color number	other
color	miscellaneous
Product details	
product component	
• cable entry	Yes
• lock	No
Mechanical Design	
height	150 mm
width	97 mm
depth	400 mm
installation width for cabinet installation	87 mm
installation depth for cabinet installation	400 mm
shape of inner subdivisions	
• shape 2a	No
• shape 2b	No
• shape 3a	Yes
• shape 3b	Yes
• shape 4a	No
• shape 4b	No
mounting position	horizontal
net weight	1.2 kg
material	sheet-steel
Certificates	
reference code according to IEC 81346-2	UC
Approvals Certificates	
General Product Approval	other



Miscellaneous



Confirmation

other	Environment	
Miscellaneous	Environmental Con- firmations	Environmental Con- firmations

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875 Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ6000-8BA12 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/8PQ6000-8BA12 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ6000-8BA12 CAX-Online-Generator http://www.siemens.com/cax Tender specifications http://www.siemens.com/specifications

last modified:

7/24/2023 

