

Datasheet

RS Pro 3301 Series 2.5mm Pitch Straight PCB Terminal Block with Push In Termination, PCB Mount, 8 Way

RS Stock No: **874-5449**



Specifications:

Body Orientation	Straight
Colour	Grey
Current Rating	2 A
Depth	13 mm
Gender	Female
Length	21.5 mm
Material	Nylon 66
Mounting Type	PCB
Number of Contacts	8
Number of Rows	1
Pitch	2.5 mm
Termination Method	Push In
Type	PCB Terminal Block
Voltage Rating	300 V
Width	12 mm



ENGLISH

American Wire Gauge	20 to 22 AWG
Insulation Withstands Voltage	2500 V ac
Operating Temperature Range	-40 to +105°C
Insulation Resistance	500 mΩ