

TVAC10050

23.6" LCD monitor with HD-SDI

The 23.6" LED monitor displays Full HD 1080p pictures in 16:9 format. Thanks to its own HD-SDI input, it is suitable for connecting to the HD-SDI camera and recorder directly – without an intermediate converter. All settings can be conveniently made using the multilingual on-screen display (OSD).

Detailed surveillance pictures in full-HD

With its high resolution in HD1080p, outstanding picture fidelity and fast reaction time, the monitor produces accurate surveillance pictures. The LED backlighting ensures optimum contrast and an extremely realistic color display. Two integrated loudspeakers and two audio inputs are also part of the features, as well as automatic signal detection and a 3D comb filter for a softer and clearer image without the annoying dot-crawl effect.

Versatile connections

Three connections ensure maximum flexibility when connecting the monitor to recorders, cameras etc. In addition to its standard connections (1x HDMI, 1x VGA, 2x BNC, 1x S-Video) the device also has a separate HD-SDI connection. Therefore the monitor is an ideal component for versatile surveillance systems.

Professional HD-SDI
surveillance

Thanks to Full HD resolution (1920 x 1080 Pixel), the monitor is perfectly suitable for connecting up devices/cameras with Full HD 1080p. The separate HD-SDI input also allows an HD-SDI devices (cameras, recorders) to be directly connected to the monitor – without HDMI converter. Furthermore, high-quality industry components ensure the monitor operates reliably for 24/7 use. The efficient LED display ensures very low power consumption.



Product highlights:

- Full HD resolution: 1920 x 1080 pixels
- HD SDI input for direct connection to an HD-SDI camera on the monitor
- HDMI and VGA input, 2x BNC, 1x S-Video
- Fast response time (1.1–3.5 ms)
- LED backlighting
- Graphical On Screen Display (OSD) for easy operation
- For wall and ceiling installation (with VESA mount)
- Integrated loudspeaker
- Low power consumption

TVAC10050

23.6" LCD monitor with HD–SDI

Easy installation

VESA standard mounts can be used to fix it to a wall or ceiling. This makes installation fast and easy.

Your Partner:
ABUS–TEST
Linker Kreuthweg 5
86444 Affing
+49 (8207) 959900
Info@abus–sc.de

TVAC10050

23.6" LCD monitor with HD-SDI

Technical Data

Monitor type	LED
Screen diagonal	23.6
Pixel pitch	0.2715 x 0.2715
Picture format	16:9
Video system	PAL / NTSC
Comb filter	3D
Signal detection	Automatisch
Contrast ratio	1.000:1
Brightness	300
Color levels	16.7
Horizontal/vertical viewing angle	160° / 170°
Reaction time	1.1 – 3.5
Frequency range	30 – 80 KHz (H) / 50–75Hz (V)
Input	1x HD-SDI, 1x HDMI, 1x VGA, 2x BNC, 1x PC-Audio, 2x Chinch Audio
Output	2x BNC, 1x HD-SDI
Loudspeaker	2 x 2,5 W
Housing material	Metal
Display surface	safety glass
DC voltage supply	12 VDC
Power consumption	3,0 A
Operating temperature	-10° – 50°
Humidity	Max. 70%
Dimensions	557 x 343 x 59

Your Partner:
ABUS-TEST
 Linker Kreuthweg 5
 86444 Affing
 +49 (8207) 959900
 Info@abus-sc.de