



6	Terminals	Brass	Silver Ptd.	5
5	Housing	ABS		1
4	"T" Holder	Steel	Nickel Ptd.	1
3	Setscrew	Steel	Nickel Ptd.	1
2	Strain Boot	PVC		1
1	Shield Cover	Zn Alloy	Nickel Ptd.	1
No.	Description	Material	Treat	Q'ty

Specifications rating :

100V AC 4A MAX

contact resistance : pins-30mΩ MAX; shell-50mΩ MAX

insulation resistance : MIN 100 MEGΩ @500V DC

voltage withstand : 250V AC R.M.S. for 1 minute

品名: ITEM :	5P180 DIN CABLE PLUG				一般公差	SHEET:	單位: unit:	mm	日期: date:	'08/03/08	繪圖: drwn by:	DanielShyr
料號: PART NO.	491144	圖號: DRW NO.			.X +/-0.25 .XX +/-0.10		比例: scale:	3 : 2	版本: version:	V. 2.0	核准: aprld by:	SkyShyr