

FEATURES

- **Heavy Duty Design:** Offers a tensile strength of 114 kg, ensuring secure bundling of heavy cables
- **Nylon Material:** Provides durability and resistance to wear and tear
- **Large Bundle Capacity:** Accommodates a maximum bundle diameter of 264 mm, suitable for large cable assemblies
- **Temperature Resistance:** Operates effectively up to 85 °C, making it suitable for various environments
- **Compliance with Standards:** Meets multiple standards including UL 94 V-2, RoHS, and CE, ensuring quality and safety

RS PRO Heavy Duty Nylon Cable Tie, 880 mm Length

RS Stock No: 656-112



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO Heavy Duty Nylon Cable Tie is designed for securing and organising cables in demanding environments. With a length of 880 mm, it is ideal for bundling large cable groups, providing a reliable and robust solution for industrial applications.

General Specifications

Colour	Natural
Product Type	Cable Tie
Sub Type	Heavy Duty Cable Tie
Tensile Strength	114 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	No

Mechanical Specifications

Length	880 mm
Material	Nylon
Maximum Bundle Diameter	264 mm
Width	12.7 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, CE 40022513, cULus E97527, DNV TAE00000US, LR 16-80006, RoHS, UL94V-2, VDE 40022513
---------------------	---