



ALPHA 630, Floor-mounted cabinet, IP43, Protection class 1, H: 1950 mm, W: 800 mm, T: 210 mm, RAL 7035, incl. flange in roof

Model			
product brand name	ALPHA 630		
product designation	Free-standing cabinet		
surface processing	powder-coated		
Protection class			
protection class IP	IP43		
operating resource protection class	Safety class 1		
suitability for interaction / lightning protection	Yes		
suitability for use / for outside use	No		
Appearance			
RAL color number	7035		
product component			
• cable entry	Yes		
• mounting plate	No		
special product feature	incl. flange in the roof		
product extension / optional / side-by-side mounting	Yes		
Mechanical Design			
height	1 950 mm		
width	800 mm		
depth	210 mm		
installation depth	210 mm		
net weight	49 kg		
material / of the enclosure	Steel		
Certificates			
reference code			
• acc. to DIN EN 61346-2	U		
• acc. to IEC 81346-2	UC		
<b>General Product Approval</b>	<b>Declaration of Conformity</b>	<b>Test Certificates</b>	<b>other</b>



[Special Test Certificate](#)

[Miscellaneous](#)

### Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8GK1322-8KA32>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8GK1322-8KA32>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1322-8KA32](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1322-8KA32)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

