

## Features

- Conductor Material: 100% copper wires
- Jacket Material: PVC, Black
- Cable Length: 0.5M
- Easy to install and reliable connection
- Color: Black

## RS PRO DC Cables

RS Stock No.: 707855



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

The 90-degree right angle plug jack cable can be easily go through the narrow gap, will never bend and damage the power supply cord. This cable is used for worn or damaged power cords, such as 12V DC power supply equipment, LED light strips, security surveillance camera systems or low voltage application systems, etc.

Current: 3A.

Voltage: 12V.

Material: 2\*0.5mm<sup>2</sup> copper wire.

Polarity distinction: Brown positive, blue negative.

Connector 1: DC 5.5mm x 2.5mm male.

Connector 2: bare wire with terminal crimped.

## General Specifications

Connector A	Male DC5.5*2.5mm
Connector A Gender	Male
Connector B	Open, terminal crimped
Connector Style	Plug, Right angle 90 degree
Outer Sheath Material	PVC
Sheath Colour	Brown, blue
Connector Plating	Nickel

## Electrical Specifications

Connection	Open end cable
Voltage Rating	12V DC
Maximum Power	3A

## Mechanical Specifications

Length	0.5m
Cable Specification	2*0.5mm <sup>2</sup> copper wire

## Operation Environment Specifications

Operating Temperature	0°C to 70°C
Storage Temperature	0°C to 70°C

## Approvals

Standards Met	RoHS, Reach
Declarations	RoHS, Reach

